



Ray Files of Bridgelux Vesta Tunable White 9mm BXRV-TR-XXXXX-10A0-B-3X Products

FTP links to ray files for Bridgelux Vesta Tunable White 9mm BXRV-TR-XXXXX-10A0-B-3X products can be found in this document. In order to download the ray files, please click on the link.

Note:

- The files are based on testing of a single array BXRV-TR-2765G-10A0-B-33 at a 50°C case temperature and at the following test currents:
 - WW(Warm White)250mA and CW(Cool White)0mA
 - WW(Warm White)125mA and CW(Cool White)125mA
 - WW(Warm White)0mA and CW(Cool White)250mA
- Customers designing on other color SKUs or at other drive or thermal conditions can use these ray files and adjust the LOP level accordingly in their design software.
- All the ray files are generated with 1M rays (IES and EUL format have 10M rays).
- All the rays are generated on a plane at z=0, which is at the center of the top surface of light emitting area. For details about where z=0 is aligned, please refer to the two photos at the end of this file, or read radiant source model in ProSource (under alignment tab).
- Please refer to the 3D CAD files of Vesta Tunable White 9mm BXRV-TR-XXXXX-10A0-B-3X products from Bridgelux website for mechanical details of the product.

Radiant Source Model with color information

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Radiant Imaging Source\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Radiant Imaging Source\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Radiant Imaging Source\)](#)

Tris-Color:

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(LightTools Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(LightTools Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(LightTools Binary Format\)](#)

Photopic:

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(ASAP Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(FRED Format\)](#)



[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(LightTools Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(LucidShape Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(OptiCAD Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Optis Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Photopia Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(SIMULUX Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(SPECTER Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(TracePro Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Zemax Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(ASAP Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(FRED Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(LightTools Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(LucidShape Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(OptiCAD Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Optis Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Photopia Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(SIMULUX Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(SPECTER Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(TracePro Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Zemax Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(ASAP Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(ASCII Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(FRED Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic Binary Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(LightTools Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(LucidShape Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(OptiCAD Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Optis Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Photopia Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(SIMULUX Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(SPECTER Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(TracePro Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Zemax Format\)](#)



Spectral (spectrum adjusted by view angle):

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Zemax Binary\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Zemax Binary\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Zemax Binary\)](#)



Spectral (spectrum adjusted by emission location):

[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(Zemax Binary\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(Zemax Binary\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic ASCII\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(FRED Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Generic Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(LightTools Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(OptiCAD\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Optis Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Photopia Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(TracePro Binary\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(Zemax Binary\)](#)

EUL and IES files:





[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(EULUMDAT Format\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW250mA CW0mA\(IES Format\)](#)

[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(EULUMDAT Format\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW125mA CW125mA\(IES Format\)](#)





[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(EULUMDAT Format\)](#)
[BXRV-TR-XXXXX-10A0-B-3X WW0mA CW250mA\(IES Format\)](#)

Alignment during radiant source model and ray file generation:

WW 250mA CW 0mA



WW 125mA CW 125mA:



WW 0mA CW 250mA:

